



HFCD14 Series Indoor/Outdoor Tight Buffer, 6 strand, I/O Tight Buffer Riser, OS2, SM , Black Jacket

By Hubbell Premise Wiring
Catalog Number [HFCD14006RSBK](#)

HFCD14 Series Indoor/Outdoor Tight Buffer, 6 strand, I/O Tight Buffer Riser, OS2, SM , Black Jacket.



Features

- Corning ULTRA SMF-28® Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	I/O Tight Buffer Riser
Color	Black
Material - Jacket	PVC
Sub Brand	Fiber Optics
Temperature Rating	-20 Degrees C to 70 Degrees C
Type	Cable
UPC	662620333854

Electrical Ratings

Wavelength 1310/1550 Nanometers

Conductor Related

Fiber Size	OS2
Fiber Type	OS2, SM
Number Of Fibers	6

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/ICEA S-83-596• NFPA-262/UL910/CSA FT-4• Telcordia GR-409 and GR-20• TIA-568.3-D
----------------------	---

Product Assets

[Catalog Page - Premise Catalog Page I-4](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-HFCD14006RSBK-SPEC-EN | REV 5/2023