

Category 6 XCELERATOR™ Jack

By Hubbell Premise Wiring
Catalog # [HXJ6B](#)



XCELERATOR™ Category 6 modular jacks exceed all TIA component level parameters to provide 5GBASE-T application assurance. The innovative angled QuickLace™ termination towers provide ample room for lacing, accelerating the termination.

Performance

TIA Cat 6 Component, Third Party Verified

General

Catalog Number	HXJ6B
Color	Blue
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Keystone
Operating Cycles	2000 Plug
Series	Cat 6 UTP
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	- Housing - High impact thermoplastic (UL 94 V-0) - IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating - Nose Contact - Beryllium copper with precious metal plating with nickel under-plating
Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact
UPC	662620825403

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	100 Ohm
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	- ANSI/TIA/EIA-568 Category 6 component - UL 1863 - Communications-Circuit Accessory - IEC60512-99-002 POE Disconnection Endurance - UL 2043 - Suitable for Air-Handling Spaces - RoHS Compliant
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Number of Pieces in Package	1
Pallet Quantity	7800

Product Assets

[Catalog Page - PREM A6 CatalogPage](#)
[Catalog Page - PREM B5 CatalogPage](#)
[Catalog Page - PREM B05 Catalog Page](#)
[Catalog Page - PREM A06 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - HDPJ High Density Jack Panels](#)
[Specifications - HXJ6B Specification Sheet French](#)
[Specifications - HXJ6B Specification Sheet English](#)