

LED Light Bulb 8.5w

Fixture mounted • Damp location listed



Description:

Maxlite 8.5W JA8 LED Lamp with an E26 base. Designed to meet Title 24 code for the State of California. The bulb is Energy Star rated and dimmable.

Specifications:

- Brightness: 800 lumens.
- 15,000 hour life (L70 standards).
- Light Appearance: 2700K (soft white).
- 3 year limited warranty.
- Dimmable to 10% brightness (See Dimming Notes)
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Input Power	8.5w
Input Voltage	120 V
Lumens/LPW (Delivered)	800/94.11 (LM-79)
CCT	2700 K
Min. Start Temp	-30 °C
Warranty	3 year limited warranty
Labels	cULus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

F8.5A19DLED927/JA8

Images:



Dimensions:

Diameter: 2.36"
Length: 2.36"
Height: 4-1/2"

F8.5A19DLED927/JA8

Dimming Notes:

F8.5A19DLED927/JA8 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron DV-603PH-WH

Lutron DV-600PR-WH

Leviton 6672 (CD-C22-06672-12A)

Leviton 6631 (CD-R70-06631-12A)

Leviton 6602 (R50-6602-1W)

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.