

One-Light Close-To-Ceiling

 Ceiling ctc mounted • Damp location listed **PROGRESS LED**


Description:

One-light LED close to ceiling with etched ribbed glass bowl and replaceable LED module in a White finish.

Specifications:

- White (-30) (painted)
- Steel Construction
- Etched ribbed glass bowl
- LED Module is replaceable (part # 93053641)
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	1023.4/60.2 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

P2305-3030K9

Images:



Dimensions:

Diameter: 13-1/4"
Height: 6-3/4"

Glass
Width: 10-3/16"
Length: 10-3/16"
Height: 4-1/2"

P2305-3030K9

Dimming Notes:

P2305 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.