

Flush Mount

 Ceiling mounted • Damp location listed **PROGRESS LED**


P2319-2030K9

Description:

One-light LED flush mount features a concentric circular pattern in an Antique Bronze metal shade that surrounds natural parchment glass. 3000K, 90+ CRI 1,211 Lumens 71.2 lumens/watt per module (source).

Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Etched Parchment glass shade
- LED Module is replaceable (part # 93053641)
- Concentric circular pattern in an Antique Bronze metal shade.
- Contemporary styling.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	782.28/47.7 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

Images:



Dimensions:

Diameter: 14"
Height: 5-3/4"

Photometrics:


P2319-2030K9

ELECTRICAL DATA	P2319-2030K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P2319-2030K9

LED Light Engine: 3000 K 90+
 System Wattage: 17
 Fixture delivered lumens: 782.28
 Fixture Efficacy: 47.7
 Spacing Criteria: 1.3



CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	174	
5	175	17
15	174	49
25	167	77
35	151	94
45	127	98
55	99	89
65	74	73
75	49	52
85	26	29
90	19	
95	18	21
105	21	22
115	25	25
125	35	32
135	46	35
145	51	32
155	51	23
165	41	12
175	27	3
180	18	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	143	18.3
0-40	237	30.3
0-60	424	54.2
0-90	578	73.9
90-120	67	8.6
90-130	99	12.7
90-150	166	21.2
90-180	204	26.1
0-180	782	100.0

Test 16.00421 Test Date 02/18/16

P2319-2030K9**Dimming Notes:**

P2319 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.