

# Project: Fixture Type: Location:

## Carrollwood

• Dry Location Only PROGRESS LED

## **Description:**

Carrollwood Collection 56-Inch Reversible Six-Blade Natural Cherry/White DC Motor Contemporary Ceiling Fan

## **Specifications:**

- · White Opal Polycarbonate Light cover
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 6 in W., 2.5 in ht., 6 in depth
- · Mounting Plate
- 80 in of wire supplied

#### **Performance:**

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,400
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only
	Meets California Title 24 JA8-2016
	DC motor

# P250074-030-30



Contact:




## **Dimensions:**

Diameter: 56 in Height: 18 in

White Opal Polycarbonate Light cover

Width: 8 in Height: 4-3/4 in





## Carrollwood

• Dry Location Only PROGRESS LED

## **Dimming Notes:**

P250074-030-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls:**

Eaton AAL06

IDevices IDEV009

Leviton 6681

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P250074-030-30