

Upshur

Ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

Upshur Collection 52 in. Antique Bronze Transitional Ceiling Fan with LED Light Kit

Specifications:

- Frosted White Acrylic Round
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6.31 in W., 2.06 in ht., 6.31 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,450/80.56 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed Meets California Title 24 JA8-2019
	AC motor

P250094-020-30



Dimensions:

Diameter: 52 in
 Height: 13-11/16 in

Frosted White Acrylic Round
 Width: 6-7/8 in
 Height: 1-15/16 in

ENERGYGUIDE

<p>Estimated Yearly Energy Cost</p> <h1 style="margin: 0;">\$9.00</h1> <p>Cost Range of Similar Models (19" – 84") <small>• Based on 12 cents per kWh and 6.4 hours use per day • Your cost depends on rates and use • Energy Use: 34 Watts</small></p>	<p>Airflow</p> <h1 style="margin: 0;">3,408</h1> <p>Cubic Feet Per Minute</p> <p><small>• The higher the airflow, the more air the fan will move • Airflow Efficiency: 102 Cubic Feet Per Minute Per Watt</small></p>
----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

All estimates based on typical use, excluding lights ftc.gov/energy

Photometrics:

P250094-020-30

ELECTRICAL DATA	P250094-020-30
Input Voltage	120/277 VAC
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	