

# LED FLUSH

Project:

Fixture Type: Location:

Contact:

Images:

Ceiling ctc mount • Damp location listed



### Specifications:

#### **Description:**

LED Flush Mount with umber glass. 120V AC replaceable module. 3000K, 90+ CRI, 1,211 lumens. Dimmable to 10% with ELV type dimmers.

### **Construction:**

- Antique Bronze (-20) (painted) •
- Etched Umber glass bowlLED Module is replaceable (part # 93053641) •
- Flicker-free dimming to 10% brightness with most ELV type dimmers .
- (See Dimming Notes) Title 24 compliant
- Ceiling pan covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- Six inches of wire supplied



P2321-2030K9

#### **Dimensions:**

Diameter: 11" Height: 4"

#### **Performance:**

| Number of Modules   | 1                                  |
|---------------------|------------------------------------|
| Input Power         | 17W                                |
| Input Voltage       | 120V                               |
| Input Frequency     | 60Hz                               |
| Lumens/LPW          | 1211/71.2 (LM-79) per module       |
| ССТ                 | 3000K                              |
| CRI                 | 90                                 |
| Life                | 60,000 (L70/TM-21)                 |
| EMI/RFI             | FCC Title 47, Part 15, Class B     |
| Min. Start Temp     | -30° C                             |
| Max. Operating Temp | 30° C                              |
| Warranty            | 5 year warranty                    |
| Labels              | cCSAus Damp location listed        |
|                     | ENERGY STAR <sup>®</sup> qualified |
|                     |                                    |

### Catalog number:

| Base  | Finish              | Color Temp         | CRI        |
|-------|---------------------|--------------------|------------|
| P2321 | 20 - Antique Bronze | <b>30K</b> - 3000K | 9 - 90 CRI |



# MOUNT



## P2321-2030K9

# LED FLUSH MOUNT

#### **Dimming Notes:**

P2321 is designed to be compatible with many Electronic Low Voltage (ELV-Reverse Phase) controls.

The following is a partial list of known compatible dimmer controls:

#### **Electronic Low Voltage ELV Reverse Phase Controls**

| Lutron  | Diva Series   | (Part Number DVELV-300P) |
|---------|---------------|--------------------------|
| Lutron  | Nova T Series | (Part Number NTELV-300)  |
| Lutron  | Vierti Series | (Part Number VTELV-600)  |
| Lutron  |               | (Part Number MAELV-600)  |
| Lutron  |               | (Part Number SPELV-600)  |
| Leviton |               | (Part Number AWRMG-EAW)  |
| Leviton |               | (Part Number 6615-P)     |
|         |               |                          |

Digital type dimmers are not recommended.

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.