




Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P250098-081 Springer II

Springer II Collection 60-in Twelve-Blade Antique Nickel Modern Farmhouse Windmill Ceiling Fan

**Category:** Ceiling Fans  
**Finish:** Antique Nickel (Painted)  
**Construction:**

Diameter.: 60 in  
Height: 16-3/16 in

MOUNTING	ELECTRICAL	ADDITIONAL INFORMATION
Ceiling downrod	80 in of wire supplied	cULus Damp Location Listed
Mounting Bracket	120 VAC	Limited Lifetime Warranty
Canopy covers a standard 4" recessed outlet box	Switch Type: Push button	

# ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

**\$6**

\$3

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 21 Watts

**Airflow**

**4,283**

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 205 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy