



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P250100-009 Brazas

Brazas Collection 56 in. Six-Blade Brushed Nickel Transitional Ceiling Fan

**Category:** Ceiling Fans  
**Finish:** Brushed Nickel (Painted)  
**Construction:**

Diameter: 56 in  
 Height: 13 in

MOUNTING	ELECTRICAL	ADDITIONAL INFORMATION
Ceiling downrod	80 in of wire supplied	UL Damp Location Listed
Mounting Bracket	120 VAC	Limited Lifetime Warranty
Canopy covers a standard 4" recessed outlet box	Switch Type: Push button	Meets California Title 24 JA8-2019

# ENERGYGUIDE

Estimated  
Yearly Energy Cost

## \$5

\$3
\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 19 Watts

Airflow

## 4,538

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 245 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy