

Billows

Ceiling Mounted • Dry Location Listed

P2552-20

Description:

The 52 inch Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades in cherry and antique walnut. With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient 9W MaxLite LED lamps, featuring a 3000K color temperature.

Specifications:

- White opal glass Bowl
- 52" Billows collection ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits
- Five reversible American Walnut/Cherry blades
- Billows collection ceiling fan with Antique Bronze finish
- Pull chain is Antique Brass with a walnut fob
- The light kit contains a white opal glass shade and is comprised of 2-9W dimmable 3000K LED lamps, offering 800 lumens/each (source), 90+ CRI
- Indoor ceiling fan ideal for use in living rooms, bedrooms and bonus rooms
- Billows ceiling fan adds form and function - by providing increased air circulation in rooms
- Features Traditional design styling
- Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- UL dry location listed
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- Can be used to comply with 2016 Title 24 JA8
- High Speed Energy Information: Airflow- 4682 cfm, Energy consumption- 59 watts (excluding lights), Airflow efficiency- 79 cfm/watt
- Limited lifetime warranty.
- Fully dimmable with dimmable bulbs.
- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 2.0625 in ht., 5.875 in depth
- Mounting bracket for outlet box included
- 54 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90+
Life (hours)	25000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry Location Listed
	AC motor



Dimensions:

Diameter: 52 in
Height: 17-1/2 in

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$10

Cost Range of Similar Models (19' - 84')

• Based on 12 cents per kWh and 6.4 hours use per day
• Your cost depends on rates and use
• Energy Use: 37 Watts

Airflow

3369

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
• Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Dimming Notes:

P2552-20 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.