

| Project: | | | |
|---------------|--|--|--|
| Fixture Type: | | | |
| Location: | | | |
| Contact: | | | |

Trevina II

Ceiling Mounted • Dry Location Listed PROGRESS LED

Description:

This ceiling fan includes an LED light source covered by a white opal shade to help extend your day into the evening. You and your family will relax in your peaceful retreat created by the cool breeze coming from the three-blades rotating overhead. The fixture is coated in a satin white finish to complete the handsome design.

Specifications:

- · White Opal glass Bowl
- You and your family will relax in your peaceful retreat created by the cool breeze coming from the three-blades rotating overhead.
- This ceiling fan includes an LED light source covered by a white opal shade to help extend your day into the evening.
- The fixture is coated in a satin white finish to complete the handsome design.
- · Ideal for any bedroom or den.
- · Perfect for modern or traditional settings.
- · Measures 44-inch width by 15-5/8-inch height.
- · Uses one LED module 18w.
- · Full dimmable
- · Includes wall control for both ceiling fan and light.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.88 in W., 2.38 in ht., 5.88 in depth
- 80 in of wire supplied

Performance:

| Number of Modules | 1 |
|---------------------|------------------------------------|
| Input Power | 18 W |
| Input Voltage | 120 V |
| Input Frequency | 60 Hz |
| Lumens/LPW (Source) | 1,600/84 (LM-82) |
| CCT | 3000 K |
| CRI | 90 CRI |
| Life (hours) | 50000 (L70/TM-21) |
| Warranty | Limited Lifetime Warranty |
| Labels | UL Dry Location Listed |
| | Meets California Title 24 JA8-2019 |
| | AC motor |

P2555-2830K




Dimensions:

Diameter: 44 in Height: 15-5/8 in

White Opal glass Bowl

Width: 8 in Height: 2 in





Trevina II

Ceiling Mounted • Dry Location Listed PROGRESS LED

Dimming Notes:

P2555-2830K

P2555-2830K is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

IDevices IDEV009

Leviton 6681

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.