

# 52" Trevina Fan

 Ceiling mounted • Dry location listed **PROGRESS LED**

## Description:

The 52 inch Trevina II features three reversible blades in medium cherry and classic walnut in Antique Bronze finish. Coolly modern, the Trevina II ceiling fan offers both form and function with an energy efficient 17W LED source with a 3000K-color temperature. Features a wall control switch.

## Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Etched Opal glass bowl
- 52" Trevina ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits
- Trevina fan features three reversible Medium Cherry/Walnut fan blades and Antique Bronze finish
- The light kit contains a etched opal glass shade and is comprised of a 17W dimmable 3000K LED module, offering 1500 lumens (source), 90+ CRI
- Includes a wall control switch
- Three speed control, manual reverse control
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Trevina ceiling fan adds form and function - by providing increased air circulation in rooms
- Features Modern and Transitional design styling
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- Includes easy to assemble canopy system that can be installed on vaulted ceilings up to 30° slope
- Ceiling mounting on downrod
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4742 cfm, Energy consumption- 64 watts (excluding lights), Airflow efficiency- 79 cfm/watt
- Limited lifetime warranty.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- 80" of wire supplied
- Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1500/88.2 (LM-82)
CCT	3000 K
CRI	90+ CRI
Life (hours)	(L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets California Title 24 JA8-2016

## P2556-2030K

### Images:



### Dimensions:

Diameter: 52"  
Height: 15-3/4"

Glass  
Width: 9-3/16"  
Height: 2-7/8"

## ENERGYGUIDE

Estimated  
Yearly Energy Cost

# \$11

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
• Your cost depends on rates and use  
• Energy Use: 39 Watts

Airflow

# 3,187

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
• Airflow Efficiency: 81 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy