

| Project: | | | |
|---------------|--|--|--|
| Fixture Type: | | | |
| Location: | | | |
| Contact: | | | |

WHIRL

Ceiling mounted • Damp location listed



Description:

Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60" Whirl fan. The stylish design comes in Antique Nickel, Antique Bronze and Forged Black finish options. The five-blade fan features an all weather damp location rating (ABS) to accommodate a variety of settings throughout the home. White opal glass shade with a 17W LED light source offers a warm 3000K-color temperature, energy savings and maintenance benefits for the home. Whirl features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. Can be used to comply with California Title 20.

Specifications:

- · Antique Nickel (-81) (Plated)
- · Steel construction
- · White opal glass Diffuser
- · Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60" Whirl fan
- The five-blade fan features an all weather damp location rating (ABS blades) to accommodate a variety of settings throughout the home
- White opal glass shade with a 17W dimmable LED light source offers a warm 3000K-color temperature, 90 CRI and 1400 lumens
- Whirl features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light.
- · Reversible motor for year round comfort allows you to choose either a down drafts (summer) or an up draft (winter)
- Add a P2630-30 wall control or P2614-30 remote control for added convenience
- $\bullet \quad \text{As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet} \\$
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 6549 cfm, Energy consumption- 70 watts (excluding lights), Airflow efficiency- 94 cfm/watt
- Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting strap for outlet box included
- · 80" of wire supplied
- · Driftwood blades, plastic construction
- · Chrome pull chain with Maple fob
- 12 degree blade pitch
- Meets California Title 24 JA8-2016

Performance:

| Number of Modules | 1 | |
|---------------------|------------------------------------|--|
| Input Power | 18w | |
| Input Voltage | 120 V | |
| Input Frequency | 60 Hz | |
| Lumens/LPW | 1386/77 (LM-79) | |
| CCT | 3000 K | |
| CRI | 90 CRI | |
| Life (hours) | 46,000 (L70/TM-21) | |
| EMI/RFI | Title 20 | |
| Min. Start Temp | -10 °C | |
| Max. Operating Temp | 40 °C | |
| Warranty | Limited Lifetime warranty | |
| Labels | UL Damp location listed | |
| | Meets California Title 24 IA8-2016 | |


P2574-8130K

Images:



Dimensions:

Diameter: 60" Height: 15-7/8"





WHIRL

Ceiling mounted • Damp location listed PROGRESS LED

P2574-8130K

Dimming Notes:

P2574 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.