

Greer

 Ceiling Mounted • Dry Location Listed **PROGRESS LED**

P2584-71

Description:

This five-blade 54 inch Greer ceiling fan complements either industrial or farmhouse décor. It comes with a wire meshed shade light kit that uses two vintage LED lamps (Included) and remote control with batteries are also included. Hang it on a flat or sloped ceiling with its dual mount system. It comes with reversible blades in driftwood and walnut.

Specifications:

- 54" Greer indoor ceiling fan features five blades and an LED light source, offering both form and function with energy- and cost-savings benefits
- Wire meshed shade light kit included that uses two vintage LED lamps (included)
- Features reversible Walnut/Driftwood blades and a Gilded Iron finish
- A hand held remote control with fan speed control and full range light dimming is included and comes with a convenient wall bracket for storage
- Remote control may be replaced by a P2630-30 wall control
- The five-blade Greer fan features a dual mount system to offer greater flexibility when installing
- The fan can be installed on a flat or sloped ceiling
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Ideal for Industrial or Farmhouse interiors
- Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- UL dry location listed for indoor use
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- High Speed Energy Information: Airflow- 4794 cfm, Energy consumption- 65 watts (excluding lights), Airflow efficiency- 82 cfm/watt
- Limited Lifetime Warranty.
- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 3.125 in ht., 5.875 in depth
- Mounting strap for outlet box included
- 80 in of wire supplied

Performance:


Input Power	6.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	450/69 (LM-82)
CCT	2200 K
CRI	90 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry Location Listed
	AC motor



Dimensions:

Diameter: 54 in

Height: 20 in



P2584-71 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

P2584-71

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered