

Description:

Two-light universal-style ceiling fan light kit features a low-profile, opal glass diffuser that's ideal for lighting in a bedroom. This fan light kit includes a threaded adapter for quick connection to most indoor ceiling fans that accept an accessory light. Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs. Polished Chrome finish.

Specifications:

- Opal glass Diffuser
- Add style and light to your ceiling fan with this universal fan light kit.
- Polished Chrome finish
- Opal glass diffuser ideal for lighting in a bedroom.
- Universal mount for Progress and other fans (threaded adapter included)
- Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Low profile design
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


P2602-15WB



Dimensions:

Diameter: 10-1/2 in
Height: 3-13/16 in

Opal glass Diffuser
Width: 10-5/8 in
Height: 3-1/4 in





Dimming Notes:

P2602-15WB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P2602-15WB