

Description:

Two-light universal-style ceiling fan light kit features a low-profile, opal glass diffuser that's ideal for lighting in a bedroom. This fan light kit includes a threaded adapter for quick connection to most indoor ceiling fans that accept an accessory light. Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs. Graphite finish.

Specifications:

- Opal glass Diffuser
- Add style and light to your ceiling fan with this universal fan light kit.
- Graphite finish.
- Opal glass diffuser ideal for lighting in a bedroom.
- Universal mount for Progress and other fans (threaded adapter included)
- Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Low profile design
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


P2602-143WB



Dimensions:

Diameter: 10-1/2 in
Height: 3-13/16 in

Opal glass Diffuser
Width: 10-5/8 in
Height: 3-1/4 in





P2602-143WB

Dimming Notes:

P2602-143WB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.