

**Description:**

Antique Bronze two-light fan kit with etched Light Umber glass bowl. Elegant light umber glass conceals light bulbs and casts an inviting illumination in any size room. Universal style lets you use with any indoor fan that accept an accessory light. Quick-connect wiring makes the installation process quick and easy.

**Specifications:**

- Tea Stained glass Bowl
- Elegant etched light umber glass bowl casts an inviting illumination.
- Antique bronze finish w/ Antique Brass pull chain and medium oak fob
- Universal style for any indoor fan that accept an accessory light.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

**Performance:**

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


**P2612-20TWB**



**Dimensions:**

Diameter: 12 in  
Height: 7-11/16 in

Tea Stained glass Bowl  
Width: 10-3/4 in  
Height: 6 in





# P2612-20TWB

## **Dimming Notes:**

---

P2612-20TWB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls:**

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.