



Description:

Spherical two-light fan light kit with -09 Brushed Nickel, and -20 Antique Bronze finials. This fixture was designed to match all the Wisten family lighting fixtures but it's clean styling goes with many other collections and styles. Universal style for use with fans that accept an accessory light comes with quick-connect wiring. Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs.

Specifications:

- Etched glass Bowl
- Add style and light to your ceiling fan with this universal fan light kit.
- Spherical, white etched glass bowl.
- Finials included are -09 Brushed Nickel, and -20 Antique Bronze.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Ideal for bedroom, den or kitchen lighting.
- Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


P2649-01WB



Dimensions:

Diameter: 12-3/4 in
 Height: 9-13/16 in

Etched glass Bowl
 Width: 11 in
 Height: 4-3/16 in





Dimming Notes:

P2649-01WB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P2649-01WB