



Description:

Antique Bronze two-light bowl fan kit with etched light topaz glass. Corresponding pull chain features an Antique Brass finish with a solid wood walnut fob. Convenient universal styling on any Progress fan comes with quick-connect wiring. Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs.

Specifications:

- Tea Stained glass Bowl
- Etched light topaz glass.
- Antique Brass pull chain w/ solid wood walnut fob included
- Antique Bronze finish
- Quick-connect wiring to any progress fan that accept an accessory light.
- Universal Style light kit for use with many fans
- Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


P2650-20TWB



Dimensions:

Diameter: 11 in
Height: 5-1/2 in

Tea Stained glass Bowl
Width: 11 in
Height: 4-1/2 in





Dimming Notes:

P2650-20TWB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P2650-20TWB