

## LED Alabaster

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

### Description:

One-Light 13" LED Alabaster Glass Flush Mount

### Specifications:

- Etched Alabaster Glass Bowl
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 13 in W., 1.625 in ht., 13 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

### Performance:


Number of Modules	1
Input Power	21 W
Input Voltage	120 V
Input Frequency	50/60 Hz
Lumens/LPW (Source)	1,716/88 (LM-82)
Lumens/LPW (Delivered)	1,231/63 (LM-79)
CCT	3000 K
CRI	90+ CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	25 °C
Warranty	5-year Limited Warranty
Labels	ETL Damp Location Listed
	Meets California Title 24 JA8-2016

# P350002-020-30



### Dimensions:

Diameter: 13 in  
 Height: 6-1/2 in



# P350002-020-30

## Dimming Notes:

---

P350002-020-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Nova T NTELV-300

Leviton\_SureSlide 6672

Leviton\_SureSlide 6674

Lutron\_Ariadni AYLV-600P

Lutron\_NTLV-600

Lutron\_Maestro MAELV-600

Lutron\_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.