

# ONE-LIGHT LED WALL SCONCE

Ceiling or wall mounted • Damp location listed



## Description:

A circular glass disc with clear edges nestles comfortably over a square frame. 12" Fixture features sleek matching finials and a frame that is finished in Architectural Bronze. Can be used as a flush mount or wall sconce.

## Specifications:

- Architectural Bronze (-129) (painted)
- Steel Construction
- White with clear edge glass disc
- LED Module is replaceable (part # 93074253)
- Circular glass disc with clear edges.
- Square frame design with sleek matching finials
- 1,770 lumens 70.8 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	25w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1770/70 (LM-82)
Lumens/LPW (Delivered)	631/25.5 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	50,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

## P350026-129-30

## Images:



## Dimensions:

Square: 12"  
Height: 2-1/4"

Glass  
Width: 12"  
Length: 12"  
Height: 0-1/8"

# ONE-LIGHT LED WALL SCONCE

Ceiling or wall mounted • Damp location listed **PROGRESS LED**



## Photometrics:

## P350026-129-30


<b>ELECTRICAL DATA</b>	<b>P350026-129-30</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.208 A
Input Power	25
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

\*See Dimming Notes for more information

### P350026-129-30

LED Light Engine: 3000 K 90+  
 System Wattage: 25  
 Fixture delivered lumens: 631  
 Fixture Efficacy: 25.5

Spacing Criteria:



Test 16.03316 Test Date 11/29/16

### CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION			FLUX		
	0.0	45.0	90.0	135.0	180.0	
0	1	1	1	1	1	
5	4	3	1	0	0	0
15	25	15	1	1	7	3
25	50	37	0	19	30	11
35	75	53	0	38	31	23
45	99	68	0	41	29	35
55	119	81	0	36	27	46
65	138	90	0	33	26	53
75	151	95	0	31	26	59
85	157	98	0	30	26	62
90	158	99	0	30	26	
95	157	98	0	30	26	62
105	151	95	0	32	26	59
115	138	90	0	35	26	54
125	120	82	0	38	27	46
135	99	69	0	42	27	35
145	75	52	0	38	30	23
155	50	36	1	15	28	10
165	24	14	0	1	3	2
175	0	1	0	0	0	0
180	0	0	0	0	0	

### ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	14	2.4
0-40	37	6.4
0-60	118	20.2
0-90	292	50.1
90-120	174	29.9
90-130	220	37.8
90-150	278	47.7
90-180	290	49.9
0-180	582	100.0

## P350026-129-30

### Dimming Notes:

---

P350026 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Cooper Devine AL DAL06P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.