

Linear Vanity

 Wall mounted • Dry location listed 

Description:

Rectangular etched opal glass fixture can be installed vertically or horizontally to accommodate modern lighting applications within the bath and vanity area. Enjoy beautiful and continuous illumination with Wedge. LED source features 3000K and 90+ CRI benefits, as well as a lifespan of more than 40,000 hours.

Specifications:

- Architectural Bronze (-129) (painted)
- Steel Construction
- Etched White glass diffuser
- Rectangular etched opal glass fixture.
- Can be installed vertically or horizontally to accommodate bath and vanity areas.
- Offers beautiful and continuous illumination.
- 622 lumens 39.4 lumens/watt per module (delivered).
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA

Performance:

Number of Modules	1
Input Power	15w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	622/39.4 (LM-79)
CCT	3000 K
CRI	93
Life (hours)	42,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	ETL Dry location listed

P2779-12930K9

Images:




Dimensions:

Width: 10-1/2"

Depth: 3-3/4"

Height: 4-3/4"

H/CTR: 2-3/8"

LED lighting facts [®]		Progress Lighting
A Program of the U.S. DOE		
Light Output (Lumens)	622	
Watts	16	
Lumens per Watt (Efficacy)	38.88	
Color Accuracy	90	
Color Rendering Index (CRI)		
Light Color	3000 (Bright White)	
Correlated Color Temperature (CCT)		
		
Warm White Bright White Daylight 2700K 3000K 4500K 6500K		
<small>All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.</small>		
Visit www.lightingfacts.com for the Label Reference Guide.		
<small>Registration Number: TH84-OP2PY4 (5/4/2016)</small>		
<small>Model Number: P2779-12930K9</small>		
<small>Type: Luminaire - Decorative</small>		

P2779-12930K9**Dimming Notes:**

P2779 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Maestro MAELV-600

Lutron Spacer system SPSELV-600

Lutron Renoir II AWRMG-EAW

Leviton SureSlide 6615-P

Lutron Maestro MAELV-600

Lutron Spacer system SPSELV-600

Lutron Renoir II AWRMG-EAW

Leviton SureSlide 6615-P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.