

Frame LED

Wall or Ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

Frame Collection One-Light 12" LED Flush Mount/Wall Sconce

Specifications:

- White With Clear Edge Glass disc
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 8.875 in W., 8.875 in ht., 0.3125 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,770/70 (LM-82)
Lumens/LPW (Delivered)	631/25.5 (LM-79)
CCT	3000 K
CRI	90+ CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2016


P350026-129-30



Dimensions:

Square: 12 in
 Height: 2-1/4 in

White With Clear Edge Glass disc
 Diameter: 12 in
 Height: 0-1/8 in



P350026-129-30


Photometrics:

ELECTRICAL DATA	P350026-129-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.208 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P350026-129-30

LED Light Engine: 3000 K 90+
 System Wattage: 25
 Fixture delivered lumens: 631
 Fixture Efficacy: 25.5

Spacing Criteria:



CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION			FLUX		
	0.0	45.0	90.0	135.0	180.0	
0	1	1	1	1	1	
5	4	3	1	0	0	0
15	25	15	1	1	7	3
25	50	37	0	19	30	11
35	75	53	0	38	31	23
45	99	68	0	41	29	35
55	119	81	0	36	27	46
65	138	90	0	33	26	53
75	151	95	0	31	26	59
85	157	98	0	30	26	62
90	158	99	0	30	26	
95	157	98	0	30	26	62
105	151	95	0	32	26	59
115	138	90	0	35	26	54
125	120	82	0	38	27	46
135	99	69	0	42	27	35
145	75	52	0	38	30	23
155	50	36	1	15	28	10
165	24	14	0	1	3	2
175	0	1	0	0	0	0
180	0	0	0	0	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	14	2.4
0-40	37	6.4
0-60	118	20.2
0-90	292	50.1
90-120	174	29.9
90-130	220	37.8
90-150	278	47.7
90-180	290	49.9
0-180	582	100.0

Test 16.03316 Test Date 11/29/16

P350026-129-30

Dimming Notes:

P350026-129-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Caseta

Lutron_Ariadni AY-600P

Lutron_Lumea LG-603PG

Leviton_SureSlide 6672

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Skylark Contour CTCL-153P

Lutron_Diva DVCL-153P

Cooper Devine AL DAL06P

Lutron_Maestro MACL-153M

Lutron_Ariadni AYLV-600P

Lutron_Maestro MA-600

Lutron_Nova T NTLV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.