

Project:

Fixture Type:

Location:

Contact:

Captarent LED

Wall Mounted • Damp Location Listed PROGRESS LED

TEISTER PROGRESS

Description:

Captarent Collection 30x36 in. Rectangular Illuminated Integrated LED White Modern Mirror


Specifications:

- Reflective Silver Glass Flat Square/Rectangular
- Diffused Glass Flat Square/Rectangular
- Dimmable to 10% brightness (See Dimming Notes)
- 59 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	30 W	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW (Delivered)	2,687/90 (LM-79)CRI 90 CRI	
Life (hours)	50000 (L70/TM-21)	
EMI/RFI	FCC Title 47, Part 15, Class B	
Warranty	5-year Limited Warranty	
Labels	cETLus Damp Location Listed	
	Meets California Title 24 JA8-2016	

P300455-030-30



Dimensions:

Width: 30 in Extends: 2 in Height: 36 in

Reflective Silver Glass Flat Square/Rectangular Width: 0-1/4 in Height: 30 in



Captarent LED

Wall Mounted • Damp Location Listed PROGRESS LED

Photometrics:

ELECTRICAL DATA	P300455-030-30	
Input Voltage	120 V	
Input Frequency	60 Hz	
THD	<20%	
EMI/RFI	FCC Title 47, Part 15, Class B	
Operating Temperature	-30 °C to 30 °C	
Dimming	Yes*	
Over-voltage, over-current, short-circuit protected		
*See Dimming Notes for more information		

P300455-030-30



Captarent LED

Wall Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

 $\mathsf{P300455}\text{-}030\text{-}30$ is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton SAL06P	
Leviton 6681	
Leviton 6672	
Leviton 6674	
Lutron NTEVL-300	
Lutron DVELV-300P	
Lutron DVCL-253P	
Lutron AYCL-153P	
Lutron SCL-153P	
Lutron TGCL-153-PH-WH	
Lutron MACL-153M	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P300455-030-30