

One-Light LED Semi-flush Mount

Ceiling mounted • Damp location listed



P350033-015-30

Description:

The one-light semi-flush fixture features industrial roots in both form and function. The Polished Chrome finish highlight the high-quality prismatic glass which adds to the historical aesthetic.

Specifications:

- Polished Chrome (-015) (plated)
- Steel Construction
- Clear Fresnel glass lens
- LED Module is replaceable (part # 93053641)
- Features a nautical-inspired Fresnel glass lens.
- Industrial roots in form and function.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	910/56.9 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

Images:



Dimensions:

Diameter: 12-1/8"

Height: 8-1/2"

Photometrics:

P350033-015-30

ELECTRICAL DATA	P350033-015-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P350033-015-30


LED Light Engine: 3000 K 90+
System Wattage: 17
Fixture delivered lumens: 910
Fixture Efficacy: 56.9
Spacing Criteria: 1.3

CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	370	
5	393	38
15	413	117
25	385	174
35	311	195
45	222	170
55	127	113
65	57	58
75	21	23
85	5	6
90	2	
95	1	1
105	0	0
115	0	0
125	0	0
135	0	0
145	0	0
155	0	0
165	0	0
175	0	0
180	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	329	36.8
0-40	524	58.6
0-60	807	90.2
0-90	894	99.9
90-120	1	0.1
90-130	1	0.1
90-150	1	0.1
90-180	1	0.1
0-180	895	100.0



Test 16.02336 Test Date 09/06/13

P350033-015-30

Dimming Notes:

P350033 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.