

# One-Light LED Flush Mount

Ceiling mounted • Damp location listed



## P350008-009-30

### Description:

One-light 19 inch LED Flush Mount in Brushed Nickel features a white linen glass bowl. Fixtures are dimmable to 10 percent with Triac, phase forward or ELV dimmers. 3000K and 90 CRI.

### Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Etched White Linen glass bowl
- 1984 lumens 67 lumens/watt (delivered)
- 3000k color temperature, 90+ CRI
- TM-21 54,000 hour life.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

### Performance:

Number of Modules	1
Input Power	30w
Input Voltage	120 V
Input Frequency	50/60 Hz
Lumens/LPW (Source)	2622/88 (LM-82)
Lumens/LPW (Delivered)	1984/67 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-25 °C
Max. Operating Temp	25 °C
Warranty	5 year warranty
Labels	ETL Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

### Images:




### Dimensions:

Diameter: 19"  
Height: 7-1/8"

Progress Lighting

LED lighting facts®

A Program of the U.S. DOE

<b>Light Output (Lumens)</b>	<b>1984</b>
<b>Watts</b>	<b>29.7</b>
<b>Lumens per Watt (Efficacy)</b>	<b>66.8</b>
<b>Color Accuracy</b>	
Color Rendering Index (CRI)	
<b>90</b>	
<b>Light Color</b>	
Correlated Color Temperature (CCT)	
<b>3000 (Bright White)</b>	
	
2700K	3000K
4500K	6500K
<small>All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.</small>	
<small>Visit <a href="http://www.lightingfacts.com">www.lightingfacts.com</a> for the Label Reference Guide.</small>	
<small>Registration Number: TH84-MMSU22 (9/13/2016)</small>	
<small>Model Number: P350008-009-30</small>	
<small>Type: Luminaire - Decorative</small>	

**P350008-009-30**

## Dimming Notes:

---

P350008 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls

---

Lutron NTELV-300

Leviton 6681

Leviton 6672

Leviton 6674

Lutron AYCL-153P

Lutron AYLV-600P

Lutron NTLV-600

Lutron MAELV-601

Leviton AWRMG-EAW

Lutron N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.