

# One-Light LED Flush Mount

 Ceiling mounted • Damp location listed **PROGRESS LED**


## P350051-020-30

### Description:

One-light 11" LED Flush Mount series featuring an etched glass bowl in an Antique Bronze finish. Fixtures are dimmable to 10 percent with Triac or ELV dimmers.

### Specifications:

- Antique Bronze (-020) (painted)
- Steel Construction
- Etched glass diffuser
- LED Module is replaceable (part # 93074038)
- 120V AC replaceable module.
- 3000k color temperature, 90+ CRI
- TM-21 60,000 hour life.
- 1452 lumens 83 lumens/watt (source).
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

### Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1452/83 (LM-82)
Lumens/LPW (Delivered)	1209/69.5 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

### Images:



### Dimensions:

Diameter: 11"  
Height: 4-3/16"

Glass  
Width: 8-15/16"  
Length: 8-15/16"  
Height: 3-7/16"

**Photometrics:**


## P350051-020-30

<b>ELECTRICAL DATA</b>	<b>P350051-020-30</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

\*See Dimming Notes for more information

**P350051-020-30**

LED Light Engine: 3000 K 90+  
 System Wattage: 17  
 Fixture delivered lumens: 1209  
 Fixture Efficacy: 69.5  
 Spacing Criteria: 1.3



**CANDELA DISTRIBUTION**

DEG	CANDELA	LUMENS
0	357	
5	356	34
15	344	97
25	320	147
35	286	179
45	241	186
55	190	170
65	137	136
75	90	96
85	56	61
90	43	
95	34	37
105	21	22
115	12	12
125	7	6
135	3	2
145	0	0
155	0	0
165	0	0
175	0	0
180	0	

**ZONAL LUMEN SUMMARY**

ZONE	LUMENS	%FIXT
0-30	278	23.5
0-40	457	38.5
0-60	813	68.5
0-90	1105	93.2
90-120	72	6.1
90-130	78	6.6
90-150	80	6.8
90-180	80	6.8
0-180	1186	100.0

## P350051-020-30

### Dimming Notes:

---

P350051 is designed to be compatible with many NEMA SSL 7a Phase Cut (forward phase) dimmers as well as many ELV (reverse phase) controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.