

# ONE-LIGHT LED WALL SCONCE

Ceiling or wall mounted • Damp location listed



## Description:

A circular glass disc with clear edges nestles comfortably over a square frame. 9" Fixture features sleek matching finials and a frame that is finished in Brushed Nickel. Can be used as a flush mount or wall sconce.

## Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- White with clear edge glass disc
- LED Module is replaceable (part # 93074039)
- Circular glass disc with clear edges.
- Square frame design with sleek matching finials
- 1,276 lumens 73 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1276/73 (LM-82)
Lumens/LPW (Delivered)	1152/67 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

## P350025-009-30

## Images:



## Dimensions:

Square: 9"  
Height: 2-1/4"

Glass  
Width: 9"  
Length: 9"  
Height: 0-1/8"

# ONE-LIGHT LED WALL SCONCE

Ceiling or wall mounted • Damp location listed



## Photometrics:


### P350025-009-30

<b>ELECTRICAL DATA</b>	<b>P350025-009-30</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

\*See Dimming Notes for more information

#### P350025-009-30

LED Light Engine: 3000 K 90+  
 System Wattage: 17  
 Fixture delivered lumens: 1152  
 Fixture Efficacy: 67  
 Spacing Criteria:



Test 16.03282 Test Date 11/29/16

#### CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION			FLUX		
	0.0	45.0	90.0	135.0	180.0	
0	0	0	0	0	0	
5	4	3	2	1	0	0
15	32	20	2	1	1	3
25	102	49	1	1	0	12
35	198	106	1	1	0	32
45	275	170	1	0	0	58
55	342	212	1	1	0	85
65	396	243	1	0	0	109
75	436	266	1	0	0	127
85	457	278	1	0	0	137
90	459	280	1	0	0	
95	458	279	0	0	0	137
105	438	267	1	0	0	128
115	401	245	1	1	0	110
125	346	214	1	0	0	86
135	282	174	0	1	0	60
145	208	116	1	1	0	34
155	116	57	1	1	0	14
165	40	26	1	1	1	4
175	0	0	0	0	0	0
180	0	0	0	0	0	

#### ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	16	1.4
0-40	48	4.2
0-60	191	16.8
0-90	564	49.7
90-120	375	33.0
90-130	460	40.5
90-150	554	48.8
90-180	572	50.3
0-180	1136	100.0

## P350025-009-30

### Dimming Notes:

---

P350025 is designed to be compatible with many NEMA SSL 7a Phase Cut (forward phase) dimmers as well as many ELV (reverse phase) controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.