

Bezel LED

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

Description:

Bezel Collection 13" LED Flush Mount

Specifications:

- Etched White Glass Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 13 in W., 0.75 in ht., 13 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,770/70 (LM-82)
Lumens/LPW (Delivered)	921/37 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2016

P350086-009-30



Dimensions:

Diameter: 13 in
 Height: 3-7/8 in

Etched White Glass Shade
 Width: 12-1/4 in
 Height: 2-7/8 in




P350086-009-30

Photometrics:

ELECTRICAL DATA	P350086-009-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.208 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P350086-009-30
 LED Light Engine: 3000 K 90 CRI
 System Wattage: 25
 Fixture delivered lumens: 921
 Fixture Efficacy: 37
 Spacing Criteria: 1.4



CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	196	
5	196	19
15	195	55
25	188	87
35	175	110
45	157	121
55	135	121
65	108	107
75	78	82
85	48	53
90	37	
95	36	39
105	33	35
115	30	30
125	25	22
135	20	15
145	14	9
155	7	3
165	2	1
175	0	0
180	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	161	17.7
0-40	270	29.7
0-60	512	56.4
0-90	755	83.0
90-120	104	11.5
90-130	127	13.9
90-150	151	16.6
90-180	155	17.0
0-180	909	100.0

Test 18.00006 Test Date 01/08/18

P350086-009-30

Dimming Notes:

P350086-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Caseta

Lutron_Ariadni AY-600P

Lutron_Lumea LG-603PG

Leviton_SureSlide 6672

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Skylark Contour CTCL-153P

Lutron_Diva DVCL-153P

Cooper Devine AL DAL06P

Lutron_Maestro MACL-153M

Lutron_Ariadni AYLV-600P

Lutron_Maestro MA-600

Lutron_Nova T NTLV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.