

# LED Flush Mount

 Ceiling mounted • Damp location listed **PROGRESS LED**


## P350080-015-30

### Description:

Fortune LED flush mount fixtures feature beautiful opal glass in an elegant form. The frame and metal fittings are finished in Polished Chrome. Fortune LED offers simple, clean lines to coordinate with Luxe, Transitional and Coastal interiors.

### Specifications:

- Polished Chrome (-015) (plated)
- Steel Construction
- Opal Inner Clear Outer Glass Bowl/Diffuser
- LED Module is replaceable (part # 93074038)
- Fortune LED flush mount fixtures feature beautiful opal glass in an elegant form
- Features 17-watt integrated LED to deliver energy savings and reduce long-term maintenance costs
- Popular Polished Chrome finish
- The frame and metal fittings feature shiny and sparkly accents for sophisticated design styling
- 1452 lumens, 83 lumens per watt (source)
- Fortune LED offers simple, clean lines to coordinate with Luxe, Transitional and Coastal interiors
- 3000K color temperature, 90CRI
- ENERGY STAR certified
- California JA8 certified.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

### Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1452/83 (LM-82)
Lumens/LPW (Delivered)	1043/58.9 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5 year limited warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

### Images:



### Dimensions:

Diameter: 16"  
Height: 7-5/8"

Glass  
Width: 7-3/4"  
Height: 5-1/4"  
Glass 2  
Width: 16"  
Length: 4"  
Height: 4"

**Photometrics:**

**P350080-015-30**

<b>ELECTRICAL DATA</b>	<b>P350080-015-30</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30°C
Dimming	Yes*

\*See Dimming Notes for more information

**P350080-015-30**


LED Light Engine: 3000 K 90 CRI  
System Wattage: 17  
Fixture delivered lumens: 1043  
Fixture Efficacy: 58.9  
Spacing Criteria: 1.4

**CANDELA DISTRIBUTION**

DEG	CANDELA	LUMENS
0	141	
5	141	13
15	138	39
25	134	62
35	127	80
45	119	93
55	111	100
65	101	100
75	90	95
85	79	86
90	74	
95	68	74
105	59	62
115	49	49
125	37	34
135	31	24
145	33	20
155	32	15
165	28	8
175	26	2
180	0	

**ZONAL LUMEN SUMMARY**

ZONE	LUMENS	%FIXT
0-30	114	12.0
0-40	194	20.3
0-60	386	40.5
0-90	666	69.8
90-120	185	19.4
90-130	219	22.9
90-150	263	27.6
90-180	288	30.2
0-180	954	100.0



Test 17.01956 Test Date 8/01/17

**P350080-015-30****Dimming Notes:**

---

P350080 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls**

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.