

## Opal-Linen LED

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

### Description:

One-Light 12" LED Opal-Linen Flush Mount

### Specifications:

- Etched Opal With Etched Linen Diffuser Glass Drum Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" recessed outlet box: 9.75 in W, 0.875 in ht., 9.75 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,452/83 (LM-82)
Lumens/LPW (Delivered)	1,023/58.8 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2016


# P350081-009-30



### Dimensions:

Diameter: 12 in  
 Height: 4-3/4 in

Etched Opal With Etched Linen Diffuser Glass Drum Shade  
 Width: 12 in  
 Height: 3-1/2 in



# P350081-009-30

## Dimming Notes:

---

P350081-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Caseta

Lutron\_Ariadni AY-600P

Leviton\_Illumatech IPI06-1LZ

Lutron\_Lumea LG-603PG

Leviton\_SureSlide 6672

Leviton\_SureSlide 6674

Lutron\_Skylark Contour CTCL-153P

Lutron\_Diva DVCL-153P

Pass & Seymour\_Harmony DCL453PTCCCV6

Lutron\_Toggler TGCL-153P

Lutron\_Maestro MACL-153M

Lutron\_Ariadni AYL-600P

Lutron\_Maestro MA-600

Lutron\_Nova T NTLV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Leviton\_Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.