

## Bezel LED

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Bezel Collection 10" LED Flush Mount

### Specifications:

- Etched White Glass Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 10.5 in W, 0.75 in ht., 10.5 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,276/73 (LM-82)
Lumens/LPW (Delivered)	659/38.1 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2016

# P350085-009-30



### Dimensions:

Diameter: 10-1/2 in  
 Height: 3-1/2 in

Etched White Glass Shade  
 Width: 9-3/4 in  
 Height: 2-1/2 in




# P350085-009-30

**Photometrics:**

<b>ELECTRICAL DATA</b>	<b>P350085-009-30</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

**P350085-009-30**  
 LED Light Engine: 3000 K 90 CRI  
 System Wattage: 17  
 Fixture delivered lumens: 659  
 Fixture Efficacy: 38.1  
 Spacing Criteria:



CANDELA DISTRIBUTION		
DEG	CANDELA	LUMENS
0	131	
5	132	13
15	132	37
25	128	59
35	120	75
45	108	83
55	92	82
65	73	73
75	54	57
85	34	37
90	26	
95	25	27
105	23	25
115	22	21
125	18	17
135	15	11
145	11	7
155	6	3
165	2	0
175	0	0
180	0	

ZONAL LUMEN SUMMARY		
ZONE	LUMENS	%FIXT
0-30	109	17.4
0-40	184	29.3
0-60	350	55.8
0-90	516	82.3
90-120	73	11.7
90-130	90	14.3
90-150	108	17.2
90-180	111	17.7
0-180	627	100.0

Test 18.00251 Test Date 3/05/18

# P350085-009-30

## Dimming Notes:

---

P350085-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Caseta

Lutron\_Ariadni AY-600P

Leviton\_Illumatech IPI06-1LZ

Lutron\_Lumea LG-603PG

Leviton\_SureSlide 6672

Leviton\_SureSlide 6674

Lutron\_Skylark Contour CTCL-153P

Lutron\_Diva DVCL-153P

Pass & Seymour\_Harmony DCL453PTCCCV6

Lutron\_Toggler TGCL-153P

Lutron\_Maestro MACL-153M

Lutron\_Ariadni AYL-600P

Lutron\_Maestro MA-600

Lutron\_Nova T NTLV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Leviton\_Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.