

## One-Light Flush Mount

 Ceiling flush mounted • Damp location listed **PROGRESS LED**


### P3659-2030K9

#### Description:

One light 14 inch LED flush mount adorned with industrial-inspired accents and etched glass. Antique Bronze finish.

#### Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Etched glass bowl
- LED Module is replaceable (part # 93053641)
- Industrial style inspired.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

#### Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	906/54.6 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

#### Images:



#### Dimensions:

Diameter: 14"  
Height: 5-1/8"

## Photometrics:

## P3659-2030K9

<b>ELECTRICAL DATA</b>	<b>P3659-2030K9</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

\*See Dimming Notes for more information

### P3659-2030K9


LED Light Engine: 3000 K 90 CRI  
 System Wattage: 17  
 Fixture delivered lumens: 906  
 Fixture Efficacy: 54.6  
 Spacing Criteria: 1.3

### CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	280	
5	279	26
15	270	76
25	251	116
35	224	140
45	188	145
55	147	132
65	107	106
75	71	75
85	44	48
90	33	
95	26	28
105	13	14
115	0	1
125	0	0
135	0	0
145	0	0
155	0	0
165	0	0
175	0	0
180	0	0

### ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	219	24.1
0-40	358	39.6
0-60	635	70.1
0-90	864	95.3
90-120	43	4.7
90-130	43	4.7
90-150	43	4.7
90-180	43	4.7
0-180	906	100.0



Test 15.00738 Test Date 05/07/15

## P3659-2030K9

### Dimming Notes:

---

P3659 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.