

#### Project:

Fixture Type: Location:

Contact:

Images:

LED Flush Mount

Ceiling mounted • Damp location listed PROGRESS LED



## **Description:**

Featuring a sleek and slim appearance, Bezel LED is an architectural series of flush mount options. Etched white glass is accented by a metal trim in a metallic finish. The glass shade is illuminated on both the bottom and sides to provide a pleasing lighted effect. 10" LED Flush Mount. Antique Bronze finish.

#### **Specifications:**

- · Antique Bronze (-020) (painted)
- Steel Construction
- Etched white Glass shade
- LED Module is replaceable (part # 93074039)
- Features a sleek and slim appearance inspired by architectural design
- One light LED flush mount
- Popular Antique Bronze finish
- · Etched white glass is accented by a metal trim in a metallic finish
- Features 17-watt integrated LED to deliver energy savings and reduce long-term maintenance costs
- The glass shade is illuminated on both the bottom and sides to provide a pleasing lighted effect
- 1276 lumens, 73 lumens per watt (source)
- 3000K color temperature, 90CRI
- ENERGY STAR certified
- California JA8 certified.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR<sup>®</sup> qualified
- Meets California Title 24 JA8-2016

### **Performance:**

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1276/73 (LM-82)
Lumens/LPW (Delivered)	659/38.1 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5 year limited warranty
Labels	cCSAus Damp location listed
	ENERGY STAR <sup>®</sup> qualified
	Meets California Title 24 JA8-2016



P350085-020-30

### **Dimensions:**

Diameter: 10-1/2" Height: 3-1/2"

Glass Width: 9-3/4" Height: 2-1/2"



# LED Flush Mount

Ceiling mounted • Damp location listed PROGRESS LED



## **Dimming Notes:**

P350085 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron Diva DVELV-300P	
Lutron Nova T NTELV-300	
Lutron Caseta	
Lutron Ariadni AY-600P	
Leviton Illumatech IPI06-1LZ	
Lutron Lumea LG-603PG	
Leviton SureSlide 6672	
Leviton SureSlide 6674	
Lutron Ariadni AYCL-153P	
Lutron Skylark Contour CTCL-153P	
Lutron Diva DVCL-153P	
Pass & Seymour Harmony DCL453PTCCCV6	
Lutron Toggler TGCL-153P	
Lutron Maestro MACL-153M	
Lutron Ariadni AYLV-600P	
Lutron Maestro MA-600	
Lutron NOVA T NTLV-600	
lutron Maestro MAELV-600	
Lutron spacer/system SPSELV-600	
Lutron Renoir II AWRMG-EAW	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.