

Three-Light LED Flush Mount

 Wall or ceiling mounted • Damp location listed **PROGRESS LED**


P3675-2030K9

Description:

18" Three-light LED flush mount with etched white opal acrylic diffuser. 3000K, 90+ CRI, 1,211 Lumens 71.2 lumens/watt per module. Acrylic bowl is attached with a twist and lock action. Can be mounted on ceiling or wall. Antique Bronze finish.

Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Etched White Opal acrylic diffuser
- LED Module is replaceable (part # 93053641)
- Three-light flush mount.
- Acrylic bowl is attached with a twist and lock action.
- Can be mounted on ceiling or wall.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	3
Input Power	17w per module
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82) per module
Lumens/LPW (Delivered)	2746/55.1 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

Images:



Dimensions:

Diameter: 18"
Height: 5-1/4"

Glass
Width: 18"
Height: 4-1/2"

P3675-2030K9

Dimming Notes:

P3675 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.