

LED Flush Mount

 Ceiling mounted • Damp location listed **PROGRESS LED**


Description:

The Fresnel LED flush mount features a nautical-inspired Fresnel glass lens, with industrial roots in form and function. Ideal for Farmhouse, Coastal and Industrial interiors. Complimented by a Oil Rubbed Bronze finish.

Specifications:

- Oil Rubbed Bronze (-108) (painted)
- Steel construction
- Etched Fresnel Glass Round
- LED Module is replaceable (part # 93074039)
- Fresnel LED flush mount
- Features an antique-inspired Fresnel glass lens, industrial roots in form and function
- 1-light 17-watt LED flush mount fixture
- Suitable for ceiling mount applications
- Measures 12 3/4" diameter x 4 1/2" H
- 937 lumens, 53.9 lumens per watt [per LM-79 (delivered)]
- Warm white 3000K lighting color, 90+CRI
- Ideal for low ceilings or small foyer spaces that showcase Farmhouse, Coastal and Industrial interiors
- Close-to-ceiling lights are natural choices for closets, hallways, and small rooms
- Replaceable light engine
- Damp location listed.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1276/73 (LM-82)
Lumens/LPW (Delivered)	937/53.9 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Warranty	5 year limited warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P350113-108-30

Images:



Dimensions:

Diameter: 12-3/4"
Height: 4-1/2"

Glass
Width: 10-1/16"
Height: 1"

Photometrics:

P350113-108-30

ELECTRICAL DATA	P350113-108-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P350113-108-30


LED Light Engine: 3000 K 90 CRI

System Wattage: 17

Fixture delivered lumens: 937

Fixture Efficacy: 53.9

Spacing Criteria: 1.16



CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	375	
5	372	35
15	353	99
25	314	145
35	263	164
45	202	156
55	142	127
65	90	90
75	50	53
85	19	22
90	9	
95	3	4
105	3	3
115	3	3
125	2	2
135	1	1
145	1	1
155	0	0
165	0	0
175	0	0
180	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	279	30.9
0-40	444	49.0
0-60	727	80.3
0-90	891	98.4
90-120	10	1.1
90-130	12	1.4
90-150	14	1.6
90-180	14	1.6
0-180	905	100.0

Test 17.03021 Test Date 11/28/17

P350113-108-30**Dimming Notes:**

P350113 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.