

Four-Light Outdoor

Wall mounted • Wet location listed



Description:

LED Wall lantern. 120/277V input voltage. Durable non-corrosive UV resistant housing and diffuser. Thermally protected LED array. 4000K.

Specifications:

- Black (-31) (painted)
- Polycarbonate Construction
- White acrylic acorn diffuser
- Thermally protected LED array. Durable non-corrosive UV resistant housing and diffuser.
- 912 lumens, 91.2 lumens/watt (delivered).
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
-
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	4
Input Power	10w per module
Input Voltage	120-277 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	912/91.2 (LM-79)
CCT	4000 K
CRI	74
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	UL-CUL Wet location listed
	Meets California Title 24 high efficacy requirements
	for outdoor use only

P3715-31

Images:



Dimensions:

Width: 6"
Depth: 6-7/8"
Height: 8-11/16"
H/CTR: 4-1/8"