

One-Light Flush Mount

Ceiling flush mounted • Damp location listed



P3610-2030K9

Description:

One-light LED flush mount combines a linen drum shade with a linen glass diffuser. 120V AC replaceable LED module, 1,211 lumens 71.2 lumens/watt per module (source). 3000K color temperature and 90+ CRI.

Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Off-White linen drum shade, Linen glass diffuser
- LED Module is replaceable (part # 93053641)
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	497/31.3 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

Images:



Dimensions:

Diameter: 10"
Height: 3-7/16"

Glass
Width: 9-13/16"
Height: 1-3/4"
Glass 2
Width: 9-3/8"
Height: 0-7/8"

Photometrics:

P3610-2030K9

ELECTRICAL DATA	P3610-2030K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P3610-2030K9

LED Light Engine: 3000 K 90 CRI

System Wattage: 17

Fixture delivered lumens: 497

Fixture Efficacy: 31.3


Spacing Criteria: 1.3

CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	159	
5	159	15
15	154	43
25	143	66
35	128	80
45	109	84
55	86	77
65	60	59
75	34	37
85	15	17
90	9	
95	5	6
105	4	4
115	3	3
125	3	3
135	2	2
145	2	1
155	1	0
165	0	0
175	0	0
180	0	0

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	125	25.1
0-40	205	41.2
0-60	366	73.6
0-90	478	96.2
90-120	13	2.6
90-130	15	3.1
90-150	18	3.7
90-180	19	3.8
0-180	497	100.0



Test 15.00753 Test Date 5/11/15

P3610-2030K9

Dimming Notes:

P3610 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.