

## One-Light Close-To-Ceiling

 Ceiling ctc mounted • Damp location listed **PROGRESS LED**


### Description:

Westport LED offers traditional styling to complement a variety of home decor options. A durable die-cast aluminum frame cradles a softly diffused seeded glass shade. 3000K, 90+ CRI 1,211 lumens 71.2 lumens/watt per module (source). One-light LED Flush Mount.

### Specifications:

- Black (-31) (powder coat paint)
- Die-cast aluminum Construction
- Etched Seeded glass shade
- LED Module is replaceable (part # 93053641)
- Traditional styling.
- Softly diffused seeded glass shade.
- Complements many home decor styles with beaded detailing.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements

### Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	808/47.8 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 high efficacy requirements

## P3883-3130K9

### Images:



### Dimensions:

Diameter: 9"  
Height: 7-1/4"

## Photometrics:

## P3883-3130K9

<b>ELECTRICAL DATA</b>	<b>P3883-3130K9</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

\*See Dimming Notes for more information

### P3883-3130K9


LED Light Engine: 3000 K 90 CRI  
 System Wattage: 17  
 Fixture delivered lumens: 808  
 Fixture Efficacy: 47.8  
 Spacing Criteria: 0.4

### CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	468	
5	326	30
15	228	64
25	144	70
35	143	90
45	153	118
55	137	122
65	105	104
75	71	76
85	45	49
90	36	
95	30	33
105	21	22
115	14	14
125	10	9
135	6	5
145	3	2
155	0	0
165	0	0
175	0	0
180	0	

### ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	164	20.3
0-40	254	31.4
0-60	494	61.1
0-90	723	89.5
90-120	69	8.6
90-130	78	9.7
90-150	85	10.5
90-180	85	10.5
0-180	808	100.0



Test 15.00488 Test Date 03/27/15

## P3883-3130K9

### Dimming Notes:

---

P3883 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron Nova T NTELV-300

Lutron Verti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.