

One-Light Flush Mount

Ceiling flush mounted • Damp location listed PROGRESS LED



Description:

One-light 8-3/8" LED flush mount with etched glass surrounded by a die-cast aluminum frame. Ideal for indoor and outdoor applications. Antique Bronze finish.

Specifications:

- Antique Bronze (-20) (painted)
- Die-cast aluminum Construction
- Frosted Seeded glass bowl
- LED Module is replaceable (part # 93053641)
- LED flush mount.
- Etched glass surrounded by a die-cast aluminum frame.
- Ideal for indoor and outdoor applications.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	742/44.4 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 high efficacy requirements for outdoor use only

P3665-2030K9

Images:



Dimensions:

Diameter: 8-3/8"

Height: 4-1/8"

Photometrics:

P3665-2030K9

ELECTRICAL DATA	P3665-2030K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P3665-2030K9

LED Light Engine: 3000 K 90 CRI

System Wattage: 17

Fixture delivered lumens: 742

Fixture Efficacy: 44.4


Spacing Criteria: 1.2

CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	219	
5	218	21
15	208	59
25	188	87
35	162	101
45	136	105
55	111	99
65	86	86
75	62	66
85	41	45
90	33	
95	26	29
105	17	19
115	13	13
125	9	8
135	4	3
145	1	1
155	0	0
165	0	0
175	0	0
180	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	166	22.4
0-40	267	36.1
0-60	472	63.7
0-90	669	90.3
90-120	60	8.1
90-130	68	9.2
90-150	72	9.7
90-180	72	9.7
0-180	742	100.0



Test 15.01351 Test Date 07/28/15

P3665-2030K9

Dimming Notes:

P3665 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.