

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3669-15

Fleet

The two-light flush mount emulates European faucet designs. Fleet is comprised of a distinct die cast arm and cup and highlighted by etched opal glass. Complimented by a Brushed Nickel finish.

- Emulates European faucet designs.
- Distinct die cast arm and cup.
- Etched opal glass.
- Includes one 6", four 12" stems and 6 Links of chain.

Category: Close-to-Ceiling

Finish: Polished Chrome (plated)

Construction: Steel Construction

Glass/Shade: Etched Opal glass bowl



Diameter: 13"
Height: 10-3/8"
Overall Ht. W/Chain: 52-1/2"

Glass
Width: 13"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain/semi-flush mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.8125" ht., 5" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Two 100w max. Medium Base E26 base porcelain sockets	UL-CUL Dry location listed 1 year warranty