

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

# P400115-031

## Seneca

Elegant simplicity is emphasized by sleek, curved, Black-finished arms in the Seneca five-light chandelier. Delicate candelabra lights appear to dance in midair as they ornament the fixture's smooth, round base. This stunning showpiece will cast a welcoming glow over energetic family meals shared at a dining table or kitchen island in modern farmhouse and luxe settings.

- Superb for providing class and light as guests are entertained at a dining table or kitchen island
- Five elegant candelabra lights appear to float in midair as they ornament the sleek, smooth frame
- The simple, sophisticated design is composed of clean lines that create generous, open space for the glowing candelabra lights
- Sleek, curved arms radiate outward from the simple orb crowning the refined fixture
- Finished in statement-making Black and accented with painted antique nickel candelabra lights
- Clean, modern design is ideal for modern farmhouse and luxe interiors
- Uses five 60-watt max candelabra base bulbs, or the LED equivalents, that are sold separately
- Measures 25-1/2 in diameter X 15-7/8 in height, Overall height with stem is 81-1/2 in, wire 180 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

**Category:** Chandeliers

**Finish:** Black (Painted)

**Construction:** Steel Construction



**Diameter:** 25-1/2"

**Height:** 15-7/8"

**Overall Ht. W/Chain And Stem:** 81-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted  Mounting Strap for outlet box included  Six links of 9 gauge chain supplied  One 6", four 12" lengths of stem included  Canopy covers a standard 4" octagonal recessed outlet box  4.75" W., 0.75" ht., 4.75" depth	Pre-wired  15 feet of wire supplied  120 V	Quantity:  Five 60w max. Candelabra Base  E12 base Phenolic sockets	cULus Dry location listed