

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400182-031 Tobin

A modern take on a classic object, Tobin's inspiration comes from the timeless mid-century forms. The tubular arms of the five-light chandelier extend outward and are made to form a gentle curve that showcase an etched white glass shade and finished in Black. The Tobin collection is ideal for those who appreciate Modern design styles.

- A modern take on a classic form - tubular arms for a gentle curve
- Etched white glass shades punctuate the sleek metallic fittings on the five-light chandelier
- Looks sharp in small foyers and entries, modern dining rooms, sunrooms and large break-fast areas
- Clean fittings and etched white glass shades make Tobin ideal for Modern interiors
- Dramatic Black finish
- Measures 27 5/8in diameter x 9 7/8in ht.
- Uses five 100-watt max. medium base bulbs or LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

**Category:** Chandeliers

**Finish:** Black (painted)

**Construction:** Steel Construction

**Glass/Shade:** Etched White glass Shades



Diameter: 27-5/8 in  
Height: 9-7/8 in  
Overall Ht. W/Chain: 70 in

Etched White glass Shades  
Width: 5 in  
Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity:	CULus Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	Five 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V	E26 base porcelain sockets	
Canopy covers a standard 4" recessed outlet box: 4.875" W., 0.875" ht., 4.875" depth			