

DATE: _____ TYPE: _____
 NAME: _____
 PROJECT: _____



Halogen

P5237-31

Spot Light

One-light low voltage spot light with sealed clear glass lens and a Black powdercoat finish. Positive adjustment with stainless steel locking screw for aiming. Stem has 1/2 IP thread for permanent installation. Mounts on stake (P5233-31), post (P8562-31) or approved weatherproof box (order separately). Units must be wired to a 12V transformer with proper capacity.

- Black powder coat finish.
- Sealed clear glass lens.
- Units must be wired to a 12V transformer with proper capacity.
- Accessory light shield (P8614-31) available.
- Accessory 45° cube cell louver (P8613-31) available.

Diameter: 5-1/4"
 Height: 5-1/4"

Category: Landscape

Finish: Black (painted)

Construction: Die-cast aluminum construction

Glass/Shade: Clear glass lens

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
1/2 IP thread mounted	Pre-wired 6" of wire supplied 12 V	Quantity: One 50w max. PAR-36 Medium base porcelain socket	UL-CUL Wet location listed 1 year warranty