

## Leawood LED

Post Mounted • Wet Location Listed **PROGRESS LED**

### Description:

Leawood Collection LED One-Light Post Lantern

### Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,276/73 (LM-82)
Lumens/LPW (Delivered)	951/53.7 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed Meets California Title 24 JA8-2016

# P540037-030-30



### Dimensions:

Diameter: 10 in  
 Height: 18-7/8 in



# P540037-030-30

## Dimming Notes:

---

P540037-030-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Caseta

Lutron\_Ariadni AY-600P

Leviton\_Illumatech IPI06-1LZ

Lutron\_Lumea LG-603PG

Leviton\_SureSlide 6672

Leviton\_SureSlide 6674

Lutron\_Skylark Contour CTCL-153P

Lutron\_Diva DVCL-153P

Pass & Seymour\_Harmony DCL453PTCCCV6

Lutron\_Toggler TGCL-153P

Lutron\_Maestro MACL-153M

Lutron\_Ariadni AYL-600P

Lutron\_Maestro MA-600

Lutron\_Nova T NTLV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Leviton\_Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.