

Pure LED

Ceiling cord Mounted • Dry Location Listed PROGRESS LED



Description:

One-light LED pendant features designer oriented details. White finish and an anodized gold interior. 3000K, 90+ CRI, 623 lumens (source).

Specifications:

- White, anodized gold inside aluminum Shade
- White acrylic Diffuser
- Designer oriented details.
- Sleek design.
- White finish with anodized gold interior.
- Dimmable to 10% with many ELV dimmers
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.125 in W., 1.0625 in depth
- Mounting strap for outlet box included
- 120 in of wire supplied

Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	323/42.5 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Dry Location Listed ENERGY STAR® qualified


P5175-3030K9



Dimensions:

Diameter: 6-1/2 in
 Height: 8-7/8 in
 Overall Ht. W/Cord: 130 in

White, anodized gold inside aluminum Shade
 Width: 6-1/2 in



Dimming Notes:

P5175-3030K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P5175-3030K9