

# Markor LED

Ceiling stem hung Mounted • Dry Location Listed PROGRESS LED



## Description:

The Markor Series is a modular pendant system. The versatile series allow the choice of shades and stem kits. This one-light LED stem mounted pendant for use with Markor Shades. Shades sold separately. This stem may be used with all Markor shades 9"-22" sizes. Includes one 6", four 12" and a 90° swivel. Brushed Nickel finish.

## Specifications:

- The Markor Series is a modular pendant system.
- One-light LED stem mounted pendant for use with Markor Shades.
- Shades sold separately.
- Includes one 6", four 12" and a 90° swivel.
- Dimmable to 10% with many ELV dimmers
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.6875 in W., 1.4375 in ht., 5.6875 in depth
- Mounting strap for outlet box included
- 120 in of wire supplied
- One

## Performance:


Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,211/71.2 (LM-82)
Lumens/LPW (Delivered)	1,039/62.6 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Dry Location Listed
	ENERGY STAR® qualified

# P5198-0930K9



## Dimensions:

Diameter: 5-3/4 in  
 Height: 5-3/8 in  
 Overall Ht. W/Stem: 62 in



# P5198-0930K9

## Dimming Notes:

---

P5198-0930K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.