

Project:			
Fixture Type:			
Location:			
Contact:			

## P550054-031

## **Irondale**

Incorporate memorable modern lighting with the industrial Irondale Collection's One-Light Black Hanging Lantern. A matte black frame features a decorative rectangular design on its top. A clear glass shade holds an etched glass diffuser ready to provide a lovely ambient glow.

- · Matte black frame features a decorative rectangular design on its top.
- · A clear glass shade holds an etched glass diffuser ready to provide a lovely ambient glow.
- · Modern light fixture with an industrial flair.
- Ideal for any foyer, entryway, patio, or porch.
- · Perfect for urban industrial or Craftsman settings.
- · Measures 9-1/2-inch width by 18-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

**Construction:** Steel Construction

Glass/Shade: Clear glass Curved Panel, Etched White glass Cylindrical



Diameter: 9-1/2 in Height: 18-1/2 in

Overall Ht. W/Chain: 93 in

Clear glass Curved Panel

Width: 2-5/8 in Height: 15 in

Etched White glass Cylindrical

Width: 5-1/2 in Height: 15-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Damp Location Listed
1/8 IP mounting plate for outlet box included	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 1" ht., 5" depth			