

# LED Mini-Pendant

 Ceiling stem mounted • Dry location listed **PROGRESS LED**


## Description:

Parlay helps further your love of nautical-inspired fashion into your decor. The tiered shade supports etched glass to offer illumination and task lighting where it's needed. 9w LED source offers energy efficiency, long life and aesthetic benefits to interior spaces. This one-light stem hung mini-pendant is in an Antique Bronze finish.

## Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Etched glass shade, Antique Bronze steel shade
- LED Module is replaceable (part # 93054049)
- Nautical-inspired design.
- Tiered shade supports etched glass to offer illumination and task lighting where it's needed.
- LED source offers energy efficiency, long life and aesthetic benefits to interior spaces.
- Includes one 6", four 12" stems and 6 links of chain.
- Dimmable to 10% with many ELV dimmers
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 10 feet of wire supplied
- One 6", four 12" lengths of stem included
- Six links of 9 gauge chain supplied
- ENERGY STAR® qualified

## Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	422/56.3 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Dry location listed ENERGY STAR® qualified

## P5329-2030K9

## Images:



## Dimensions:

Diameter: 8"  
 Height: 7-5/8"  
 Overall Ht. W/Stem: 73-1/2"

Glass  
 Width: 3-11/16"  
 Length: 3-11/16"  
 Height: 4-7/8"  
 Glass 2  
 Width: 8"  
 Length: 8"  
 Height: 0-15/16"

**P5329-2030K9****Dimming Notes:**

---

P5329 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls**

---

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.